



Powering Business Worldwide

pe.eaton.com

D4 Series General Purpose Plug-In Relay

D4PR2B

UPC:782114227947

Dimensions:

- **Height:** 1.1 IN
- **Length:** 1.14 IN
- **Width:** .51 IN

Weight: .5 LB

Notes: Indicator lamp available. Consult sales office or customer support center for additional coil voltages.

Warranties:


- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 5A
- **Coil Voltage:** 240V
- **Contact Configuration:** DPDT
- **Cover:** Plain
- **Inductive Full Load:** 2A, 250 Vac/3A, 30 Vdc
- **Maximum Voltage:** 380 Vac/125 Vdc
- **Quantity:** 50
- **Resistive Load:** 5A, 240 Vac/30 Vdc
- **Series:** D4 series

Supporting documents:

- [Eaton's Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [D4_R2 3D Inventor](#)
- [Eaton Specification Sheet - D4PR2B](#)
- [D4_R2 AutoCAD 2D Footprint](#)
- [D4_R2 2D Drawing Xchange](#)



- [D4_R2 3D Model Xchange](#)
- [D4_R2 2D PDF](#)
- [D4_R2 AutoCAD 2D Footprint \(mm\)](#)

Certifications:

- UL Listed file E65657
- cRUus
- CSA file No. LR701519
- UL Listed file E1491

Product compliance:

- RoHS Compliant
- CE Marked