



Powering Business Worldwide

pe.eaton.com

Comet Series Tubular Photoelectric Sensor

13102A6513

UPC:782113928180

Dimensions:

- **Height:** 2.6 IN
- **Length:** .47 IN
- **Width:** .71 IN

Weight:.2875 LB

Warranties:

- 3 year

Specifications:

- **Connection:** 6.6 Ft. (2m) Cable
- **Contact Rating:** 300 mA AC/DC at 20-264Vac/15-30Vdc
- **Cable Type:** PVC
- **Contact Configuration:** AC: L1 Switched, DC: NPN Open Collector
- **Cord Length:** 79.2 FT
- **Diameter:** .71 IN
- **Enclosure Material:** Lens: Polycarbonate
Cable Jacket: PVC Body: Structural Polyurethane Foam
- **Environmental Rating:** NEMA 1,3,4,4X,6,6P,12,13, IP68, IP69K
- **Input Voltage:** 20-264 Vac/15-30 Vdc
- **Led Indicators:** Red output status
- **Maximum Ac Current:** 300 mA
- **Operating Mode:** Focused Spot Diffuse
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Protection:** Latching short circuit
- **Sensor Type:** focused Diffuse
- **Switch Type:** Photoelectric



Supporting documents:

- [Comet series - Photoelectric sensors](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 13102A6513](#)

Certifications:

- UL Recognized
- cUL Recognized

Product compliance:

- CE Marked
- Contact Manufacturer

© 2016 Eaton. All rights reserved.