



Powering Business Worldwide

pe.eaton.com

Comet Series Tubular Photoelectric Sensor

14101RF0917-R

UPC:782113932514

Dimensions:

- **Height:** 3 IN
- **Length:** .47 IN
- **Width:** .71 IN

Weight:.2875 LB

Warranties:

- 3 year

Specifications:

- **Connection:** 9 Ft. (2.7m) Cable
- **Contact Rating:** 100 mA PNP, 250 mA NPN at 10-30 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** NPN and PNP Open Collector
- **Cord Length:** 108 FT
- **Diameter:** .71 IN
- **Enclosure Material:** Lens: Polycarbonate
Cable Jacket: PVC Body: Structural Polyurethane Foam
- **Environmental Rating:** NEMA 1,3,4,4X,6,6P,12,13, IP68, IP69K
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 100 mA PNP, 250 mA NPN
- **Operating Mode:** Polarized Retroreflective
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Protection:** Auto reset short circuit
- **Switch Type:** Photoelectric



Supporting documents:

- [Eaton Specification Sheet - 14101RF0917-R](#)

Certifications: No Data**Product compliance:**

- Contact Manufacturer

© 2016 Eaton. All rights reserved.