



Powering Business Worldwide

pe.eaton.com

50 Series Photoelectric Sensor

1350B-6507

UPC:782113823621

Dimensions:

- **Height:** 3.19 IN
- **Length:** 1.64 IN
- **Width:** 1.83 IN

Weight: .2625 LB

Notes: Ranges based on 3-inch retroreflector for reflex sensors; 90% reflectance card for diffuse reflective sensors

Warranties:

- 3 year

Specifications:

- **Connection:** 4 Pin Dual Key Micro Connector
- **Contact Rating:** 250 mA at 30 Vdc
- **Contact Configuration:** NPN and PNP Open Collector
- **Enclosure Material:** Body: Noryl, Lens: Nylon
- **Environmental Rating:** NEMA 1,3,4,12,13
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 250 mA
- **Operating Mode:** Diffuse Reflective
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Protection:** Reverse polarity
- **Switch Type:** Photoelectric

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 1350B-6507](#)

Certifications:

- UL Listed
- CSA Certified



Product compliance:

- Contact Manufacturer

© 2016 Eaton. All rights reserved.