



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Industrial Control Transformer

**C0350E4CFB**

**UPC:**786680001178

### Dimensions:

- **Height:** 5.197 IN
- **Length:** 5.236 IN
- **Width:** 4.488 IN

**Weight:**13.8 LB

**Notes:**Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Coil Material:** Copper windings
- **Design:** MTE
- **Modification 1:** Factory-mounted 2-pole primary fuse block for rejection type fuses
- **Primary Voltage:** 550/575/600V
- **Secondary Voltage:** 110/115/120V
- **Tap Size:** None
- **Temperature Rating:** 55°C
- **Type:** Industrial Control Transformer
- **Volt Ampere Rating:** 350 VA

### Supporting documents:

- [Control Transformer Final Assembly - C0350E4CFB](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)



- [Eaton Specification Sheet - C0350E4CFB](#)

**Certifications:**

- cUL Certified
- UL Listed
- CSA Certified

**Product compliance:**

- RoHS Compliant

---

© 2016 Eaton. All rights reserved.