



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Comet Series Tubular Photoelectric Sensor

14101AS6515

UPC:782114414880

### Dimensions:

- **Height:** 2.64 IN
- **Length:** .47 IN
- **Width:** .71 IN

**Weight:** .2875 LB

**Notes:** Ranges based on a 3-inch diameter retroreflector (not included). Polarized Reflex Sensors may not operate with retroreflective tape. Test selected tape prior to installation.

### Warranties:

- 3 year

### Specifications:

- **Connection:** 6.6 Ft. ( 2m ) Cable
- **Contact Rating:** 300 mA at 90-132 Vac/18-50 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** 2 Wire AC/DC
- **Cord Length:** 79.2 FT
- **Diameter:** .71 IN
- **Enclosure Material:** Lens: Polycarbonate  
Cable Jacket: PVC Body: Structural Polyurethane Foam
- **Environmental Rating:** NEMA 1,3,4,4X,6,6P,12,13, IP68, IP69K
- **Input Voltage:** 90-132 Vac/18-50 Vdc
- **Led Indicators:** Red output status
- **Maximum Ac Current:** 300 mA
- **Operating Mode:** Polarized Retroreflective
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)



- **Protection:** Latching short circuit
- **Switch Type:** Photoelectric

**Supporting documents:**

- [Comet series - Photoelectric sensors](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 14101AS6515](#)

**Certifications:**

- UL Recognized
- cUL Recognized

**Product compliance:**

- CE Marked
- Contact Manufacturer