



Powering Business Worldwide

pe.eaton.com

Type F Special Purpose Limit Switch

10316H320

UPC:782113229218

Dimensions:

- **Height:** 7.69 IN
- **Length:** 3.31 IN
- **Width:** 3.75 IN

Weight:3.57 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** AC: Make 40A Break 15A at 120Vac DC: Break 0.5A
- **Contact Configuration:** 2NO-2NC
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 4
- **Maximum Ac Current:** 40A
- **Maximum Dc Current:** 0.5A
- **Operating Temperature:** 0° to 180°F (-18° to 82°C)
- **Switch Type:** Side Rotary, Type F

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 10316H320](#)

Certifications:

- UL Listed

Product compliance:

- Contact Manufacturer

