



Powering Business Worldwide

pe.eaton.com

E58 Harsh Duty Series Tubular 30mm Photoelectric Sensor

E58-30DP150-ELPB

UPC:782114234365

Dimensions:

- **Height:** 4.36 IN
- **Length:** 1.18 IN
- **Width:** 1.18 IN

Weight:.2688 LB

Warranties:

- 3 year

Specifications:

- **Connection:** 3 Pin Mini Pigtail Connector
- **Contact Rating:** 300 mA at 90-132Vac/18-50Vdc
- **Cable Type:** PVC
- **Contact Configuration:** 2 Wire AC/DC
- **Cord Length:** 7 IN
- **Diameter:** 1.18 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** NEMA 1,2,3,3R,3S,4,4X,6,6P,12,13 and IP69K
- **Input Voltage:** 90-132Vac/18-50Vdc
- **Led Indicators:** Red Output Status
- **Maximum Ac Current:** 300 mA
- **Operating Mode:** Background Suppression
- **Operating Temperature:** -13° to 131°F (-25° to 55°C)
- **Protection:** Auto reset short circuit
- **Sensor Type:** Back Ground Suppression
- **Switch Type:** Photoelectric

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Test the Best Photoelectric Sensors: E58](#)



Series Harsh Duty

- Eaton Specification Sheet - E58-30DP150-ELPB

Certifications: No Data

Product compliance: No Data

© 2016 Eaton. All rights reserved.