



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Inductive Proximity Tubular Sensor

**E55CAL30T111**

**UPC:**782113888309

### Dimensions:

- **Height:** 1.18 IN
- **Length:** 3.15 IN
- **Width:** 1.18 IN

### Warranties:

- 1 year

### Specifications:

- **Type:** Inductive Proximity Tubular Sensor
- **Contact Rating:** 200 mA
- **Cable Type:** PVC
- **Contact Configuration:** NO PNP open collector
- **Cord Length:** 79.2 FT
- **Diameter:** 1.18110237 MM
- **Enclosure Material:** PBT
- **Environmental Rating:** NEMA 3, 3S, 4, 4X, 13, IP66
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Output ON
- **Number Of Wires:** 3-wire
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** S/C and reverse polarity
- **Series:** E55

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E55CAL30T111](#)

**Certifications:** No Data

**Product compliance:** No Data



