



Powering Business Worldwide

pe.eaton.com

30.5 mm, Class I Division 2 Selector Switch Operator

10250T5971H

UPC:782114523100

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes: Operator includes lens gasket and lens attachment screws

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Class I Division 2
- **Cam Code:** Cam 1
- **Illumination:** Illuminated
- **Light Unit Type:** Incandescent, transformer
- **Number Of Positions:** Two-position
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T
- **Throw Type:** 60°
- **Voltage Rating:** 120 Vac with 6 Volt Lamp

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T5971H](#)

Certifications: No Data

Product compliance: No Data

