



Powering Business Worldwide

pe.eaton.com

E57 Small Diameter Series Inductive Proximity Sensor

E57LAL8T110ED

UPC:782113628806

Dimensions:

- **Height:** 2 IN
- **Length:** .31 IN
- **Width:** .31 IN

Weight:.05 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 1%
- **Connection:** 4 Pin M12 Connector
- **Contact Rating:** 200 mA at 30 Vdc
- **Contact Configuration:** NPN Open Collector, Normally Open
- **Diameter:** .315 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12 and 13 (IP67)
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 200 mA
- **Operating Mode:** Un-shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Short circuit protected
- **Sensor Type:** Inductive Proximity

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57LAL8T110ED](#)

Certifications: No Data



Product compliance: No Data

© 2016 Eaton. All rights reserved.