



Powering Business Worldwide

pe.eaton.com

Capacitive Proximity Sensor Body

E53KAL30A2SA

UPC:782114012901

Dimensions:

- **Height:** 1.18 IN
- **Length:** 3.94 IN
- **Width:** 1.18 IN

Warranties:

- 1 year

Specifications:

- **Type:** Threaded
- **Connection:** Dual key micro
- **Contact Rating:** 300 mA Solid State Output
- **Contact Configuration:** 2-wire AC, NO
- **Diameter:** 1.18110237 MM
- **Enclosure Material:** POM, mounting nuts, nylon PA66
- **Environmental Rating:** NEMA 1, 2, 3, 3S, 4, 12, 13, IP65
- **Input Voltage:** 20-250V
- **Led Indicators:** Output ON
- **Maximum Ac Current:** 300 mA
- **Number Of Pins:** 3 pin
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Series:** E53

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Sensing solutions-versatile, robust and innovative](#)
- [Eaton Specification Sheet - E53KAL30A2SA](#)

Certifications: No Data



Product compliance: No Data

© 2016 Eaton. All rights reserved.