



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E58 Harsh Duty Series Tubular 30mm Photoelectric Sensor

**E58-30TS250-GA3**

**UPC:**782113491998

### Dimensions:

- **Height:** 4.36 IN
- **Length:** 1.18 IN
- **Width:** 1.18 IN

**Weight:**.7563 LB

### Warranties:

- 3 year

### Specifications:

- **Connection:** 9.8 Ft. ( 3m ) Cable
- **Cable Type:** PVC
- **Cord Length:** 120 FT
- **Diameter:** 1.18 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** NEMA  
1,2,3,3R,3S,4,4X,6,6P,12,13 and IP69K
- **Input Voltage:** 20-132 Vac 50/60 Hz or 15-30  
Vdc
- **Led Indicators:** Red Power On Status
- **Operating Mode:** Thru-Beam
- **Operating Temperature:** -40° to 131°F (-40° to  
55°C)
- **Sensor Type:** Through Beam
- **Switch Type:** Photoelectric

### Supporting documents:

- [Eaton Specification Sheet - E58-30TS250-GA3](#)

**Certifications:** No Data

**Product compliance:** No Data



