



Powering Business Worldwide

pe.eaton.com

E58 Harsh Duty Series Tubular 30mm Photoelectric Sensor

E58-30TS250-GA8

UPC:782113492025

Dimensions:

- **Height:** 4.36 IN
- **Length:** 1.18 IN
- **Width:** 1.18 IN

Weight:2.1563 LB

Warranties:

- 3 year

Specifications:

- **Connection:** 26.2 Ft. (8m) Cable
- **Cable Type:** PVC
- **Cord Length:** 312 FT
- **Diameter:** 1.18 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** NEMA
1,2,3,3R,3S,4,4X,6,6P,12,13 and IP69K
- **Input Voltage:** 20-132 Vac 50/60 Hz or 15-30
Vdc
- **Led Indicators:** Red Power On Status
- **Operating Mode:** Thru-Beam
- **Operating Temperature:** -40° to 131°F (-40° to
55°C)
- **Sensor Type:** Through Beam
- **Switch Type:** Photoelectric

Supporting documents:

- [Eaton Specification Sheet - E58-30TS250-GA8](#)

Certifications: No Data

Product compliance: No Data



