



Powering Business Worldwide

pe.eaton.com

Type NB Tri-Pac Thermal-Magnetic Circuit Breaker

NB3600PT

UPC:786679358559

Dimensions:

- **Height:** 22 IN
- **Length:** 5.5 IN
- **Width:** 8.25 IN

Weight:4 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Trip unit only
- **Amperage Rating:** 600A
- **Interrupt Rating:** 200 kAIC at 600 Vac, 100 kAIC at 250 Vdc
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 600V
- **Magnetic Trip Range:** 3000-6000A

Supporting documents:

- [Miniature and Molded Case Circuit Breakers](#)
- [Eaton Specification Sheet - NB3600PT](#)

Certifications:

- UL 489

Product compliance: No Data

