



Powering Business Worldwide

pe.eaton.com

30.5 mm, Class I Division 2, Assembled Push-Pull Unit

10250T871GD

UPC:782114521151

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Class I Division 2
- **Actuator:** Standard
- **Actuator Color:** Green
- **Bus Material:** Plastic
- **Contact Configuration:** 2NC
- **Illumination:** Illuminated
- **Light Unit Type:** Incandescent, full voltage
- **Light Unit Voltage:** 24 Vac/dc
- **Number Of Positions:** Three-position
- **Operating Mode:** Maintained push, momentary pull
- **Size:** 40 mm
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D
- **Series:** 10250T

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T871GD](#)

Certifications:

- UL 508
- CSA Certified
- UL 1604



Product compliance:

- FDA 3-A
- CE Marked

© 2016 Eaton. All rights reserved.