



Powering Business Worldwide

pe.eaton.com

Limit Switch Body Mini Connector

E50SA6PC

UPC:782113726403

Dimensions:

- **Height:** 2.46 IN
- **Length:** 4.24 IN
- **Width:** 1.54 IN

Warranties:

- 1 year

Specifications:

- **Connection:** Mini
- **Contact Rating:** 10A at 240 Vac, 1A at 250 Vdc
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, IP69K
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1A
- **Number Of Pins:** 5 pin
- **Number Of Poles:** Single-pole
- **Operating Temperature:** -40° to 250°F (-40° to 121°C)
- **Series:** E50 Heavy Duty Factory Sealed 6P+

Supporting documents:

- [Eaton's Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50SA6PC](#)

Certifications:

- UL Recognized
- CSA Certified

Product compliance: No Data



