



Powering Business Worldwide

pe.eaton.com

30.5 mm, Heavy-Duty Selector Switch Operator

10250T6303

UPC:782113295732

Dimensions:

- **Height:** 2.4 IN
- **Length:** 3.4 IN
- **Width:** 1.9 IN

Weight: .4 LB

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Cam Code:** Cam 3
- **Illumination:** Illuminated
- **Light Unit Type:** Incandescent, full voltage
- **Number Of Positions:** Three-position
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T
- **Throw Type:** 60°
- **Voltage Rating:** 208 Vac/dc

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T6303](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- CE Marked

