



Powering Business Worldwide

pe.eaton.com

22.5 mm, Non-metallic Heavy-Duty Pushbutton Operator

E22TB9X27

UPC:782113553382

Dimensions:

- Height: X
- Length: X
- Width: X

Notes:Maximum of 2 contact blocks (4 circuits) when used with supplied 3-way adapter

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** 22.5 mm, Non-metallic Heavy-Duty
- **Actuator:** Extended
- **Actuator Color:** Amber
- **Actuator Material:** Plastic
- **Bezel:** Black
- **Enclosure:** NEMA 3, 3R, 4, 4X, 12, 13
- **Illumination:** Illuminated
- **Lamp Voltage:** 6 Vac
- **Led Lamp Number:** #755
- **Light Unit Type:** Incandescent, transformer
- **Light Unit Voltage:** 120 Vac
- **Operating Mode:** Momentary
- **Size:** 25 mm
- **Series:** E22

Supporting documents:

- [Pushbuttons, Indicating lights, Selector switches and Stacklights](#)
- [Eaton Specification Sheet - E22TB9X27](#)



Certifications:

- IEC 947-5-1 MTTA
- UL 508
- CSA Certified
- Lloyd's Register Certified

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.