



Powering Business Worldwide

pe.eaton.com

E57 Premium+ Series Short Body Tubular Inductive Proximity Sensor

E57SAL18A2S5

UPC:782113965178

Dimensions:

- **Height:** 2.54 IN
- **Length:** .71 IN
- **Width:** .71 IN

Weight:.4156 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 3%
- **Connection:** 16 Ft. (5m) Cable
- **Contact Rating:** 250 mA at 40-240Vac/20-250Vdc
- **Cable Type:** PVC
- **Contact Configuration:** 2 - Wire AC/DC, Normally Open
- **Cord Length:** 192 FT
- **Diameter:** .71 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** IP67, IP69K NEMA 4, 4X, 6, 6P
- **Input Voltage:** 40–250 Vac/20–250 Vdc
- **Led Indicators:** Red output status
- **Maximum Ac Current:** 250 mA
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Short circuit protected
- **Sensor Type:** Inductive Proximity

Supporting documents:



- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57SAL18A2S5](#)

Certifications: No Data

Product compliance: No Data

© 2016 Eaton. All rights reserved.