



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Comet Series Tubular Photoelectric Sensor

13104RF1215

UPC:782113937564

### Dimensions:

- **Height:** 3.02 IN
- **Length:** .6 IN
- **Width:** .71 IN

**Weight:** .2875 LB

### Warranties:

- 3 year

### Specifications:

- **Connection:** 15 Ft. ( 4.6m ) Cable
- **Contact Rating:** 300 mA at 90-132 Vac/18-50 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** 2 Wire AC/DC
- **Cord Length:** 8 IN
- **Diameter:** .71 IN
- **Enclosure Material:** Lens: Polycarbonate  
Cable Jacket: PVC Body: Structural Polyurethane Foam
- **Environmental Rating:** NEMA 1,3,4,4X,6,6P,12,13, IP68, IP69K
- **Input Voltage:** 90-132 Vac/18-50 Vdc
- **Led Indicators:** Red output status
- **Maximum Ac Current:** 300 mA
- **Operating Mode:** Background Suppression
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Auto reset short circuit
- **Sensor Type:** Back Ground Suppression
- **Switch Type:** Photoelectric

### Supporting documents:



- [Eaton Specification Sheet - 13104RF1215](#)

**Certifications:** No Data

**Product compliance:**

- Contact Manufacturer

---

© 2016 Eaton. All rights reserved.