



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Mini Complete Limit Switch

E49G31AP3

UPC:782113983073

### Dimensions:

- **Height:** 1.62 IN
- **Length:** 4.93 IN
- **Width:** 1.1 IN

### Warranties:

- 1 year

### Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 5A at 250 Vac, 5A at 30 Vdc
- **Actuator:** Side rotary lever
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Cast zinc
- **Environmental Rating:** IP65
- **Maximum Ac Current:** 5A continuous
- **Maximum Dc Current:** 5A at 30 Vdc
- **Operating Speed:** 5 mm-50 cm/s
- **Operating Temperature:** 23° to 149°F (-5° to 65°C)
- **Series:** E49

### Supporting documents:

- [E49 Mini Metal Limit switches](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E49G31AP3](#)

**Certifications:** No Data

**Product compliance:** No Data

