



Powering Business Worldwide

pe.eaton.com

E47 Precision Limit Switch, Basic

E47CMS02

UPC:782114397534

Dimensions:

- **Height:** 1.94 IN
- **Length:** .69 IN
- **Width:** 1.35 IN

Weight:.0813 LB

Notes:Bottom facing M4 x 0.7 (8-32) terminal screws with cup washers will accept 22 -12 AWG (2.5 sq. mm maximum)

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 20A at 125Vac / 20A at 14Vdc
- **Contact Configuration:** SPDT
- **Enclosure Material:** Mineral Filled Phenolic
- **Environmental Rating:** NEMA 1
- **Maximum Ac Current:** 20A
- **Operating Temperature:** -13° to 176°F (-25° to 80°C)
- **Switch Type:** Straight Plunger

Supporting documents:

- [E47 precision - Limit switches](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E47CMS02](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- CE Marked



