



Powering Business Worldwide

pe.eaton.com

Precision Limit Switch

E47CMS22

UPC:782114350805

Dimensions:

- **Height:** 1.5 IN
- **Length:** 2.94 IN
- **Width:** .69 IN

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 20A at 250 Vac, 6A at 30 Vdc
- **Actuator:** Straight lever
- **Contact Configuration:** 1-SPDT (Form C)
- **Enclosure Material:** Mineral filled phenolic
- **Environmental Rating:** NEMA 1
- **Maximum Ac Current:** 20A
- **Operating Speed:** 0.01 mm/s-1m/s
- **Operating Temperature:** -13° to 176°F (-25° to 80°C)
- **Series:** E47

Supporting documents:

- [E47 precision - Limit switches](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E47CMS22](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance: No Data

