



Powering Business Worldwide

pe.eaton.com

Heavy Duty 6-Pole Motor Circuit Safety Switch

DH662FDK

UPC:782113370484

Dimensions:

- **Height:** 9 IN
- **Length:** 25.5 IN
- **Width:** 13.25 IN

Weight:40 LB

Notes:Can be field modified to meet NEMA 3R rainproof requirements when a factory provided drain hole is opened

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 60A
- **Enclosure:** NEMA 12
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible without neutral
- **Number Of Poles:** Six-pole
- **Number Of Wires:** Six-wire
- **Product Category:** Heavy Duty 6-Pole Motor Circuit Safety Switch
- **Voltage Rating:** 600V
- **Max Hp Rating:** 20 at 480 Vac TD 1 Ph, 25 at 600 Vac TD 1 Ph, 15 at 240 Vac TD 3 Ph, 30 at 480 Vac TD 3 Ph, 50 at 600 Vac TD 3 Ph

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)



- [Heavy-Duty Safety Switch with Bussmann CUBEFuse Fuse Clips](#)
- [Eaton Specification Sheet - DH662FDK](#)

Certifications:

- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.