



Powering Business Worldwide

pe.eaton.com

22.5 mm, Non-metallic Heavy-Duty Pushbutton Operator

E22LTA2N123

UPC:782114980446

Dimensions:

- **Height:** 1.5 IN
- **Length:** 3.5 IN
- **Width:** 3 IN

Weight: .16 LB

Notes: EMO (Emergency Machine Shut Off) marking per SEMI S2 Requirement.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** 22.5 mm, Non-metallic Heavy-Duty
- **Actuator:** Trigger action
- **Actuator Color:** Red
- **Contact Configuration:** 1NC
- **Enclosure:** NEMA 3, 3R, 4, 4X, 12, 13
- **Illumination:** Non-illuminated
- **Legend:** EMO
- **Letter Color:** White
- **Light Unit Type:** No light unit
- **Operating Mode:** Twist-to-release
- **Size:** 40 mm
- **Series:** E22

Supporting documents:

- [Eatons Volume 12-Aftermarket, Renewal Parts and Life Extension Solutions](#)
- [Pushbuttons, Indicating lights, Selector switches and Stacklights](#)



- [Eaton Specification Sheet - E22LTA2N123](#)

Certifications:

- CSA Certified
- EN 418
- UL 508
- IEC 947-5-1 MTTA
- Lloyd's Register Certified

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.