



Powering Business Worldwide

pe.eaton.com

E47BCC Series Compact Pre-Wired Limit Switch

E47BCC13

UPC:782114215449

Dimensions:

- **Height:** 2.64 IN
- **Length:** 1.58 IN
- **Width:** .69 IN

Weight:.825 LB

Warranties:

- 1 year

Specifications:

- **Connection:** 10 Ft. (3m) Cable
- **Contact Rating:** 5A at 240 Vac/5A at 14 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** SPDT
- **Cord Length:** 120 FT
- **Enclosure Material:** Die Cast Aluminum
- **Environmental Rating:** NEMA 4, 6 and 13 IEC IP67
- **Maximum Ac Current:** 5A
- **Operating Temperature:** 14° to 158°F (-10° to 70°C)
- **Switch Type:** Bevel Plunger

Supporting documents:

- [Eaton's Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E47BCC13](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance:

- CE Marked



