



Powering Business Worldwide

pe.eaton.com

E49 Miniature DIN Limit Switch, Plastic Body

E49S74UP7

UPC:782114982860

Dimensions:

- **Height:** 5.61 IN
- **Length:** 1.22 IN
- **Width:** 2.19 IN

Weight:.2313 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 600Vac, 1.5A at 24Vdc
- **Switch Type:** Adj. Side Rotary
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Self-extinguishing PA-6 (Glass-reinforced, Polyamide)
- **Environmental Rating:** NEMA 4, 4X, 6P, 13 (IP65)
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1.5A
- **Operating Temperature:** -22° to 176°F (-30° to 80°C)

Supporting documents:

- [Eaton Specification Sheet - E49S74UP7](#)

Certifications: No Data

Product compliance: No Data

