



Powering Business Worldwide

pe.eaton.com

C25 Definite Purpose Control Starter

A25CNC25A

UPC:782113757865

Dimensions:

- **Height:** 3.69 IN
- **Length:** 7.14 IN
- **Width:** 2.5 IN

Weight:3.6 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Accessories:** Mounting plate
- **Model:** Open
- **Options:** Individual pkg.
- **Auxiliary Contact:** Pressure plate
- **Coil Voltage:** 110-120 Vac, 50/60 Hz
- **Frame Size:** Compact, single-pole w/shunt
- **Number Of Poles:** Three-pole
- **Phase:** Three-phase
- **Series:** D1
- **Terminals:** Screw
- **Type:** Non-reversing

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - A25CNC25A](#)

Certifications:

- CSA file No. LR353 Guide380W-1.14 (Class 3211 04)
- UL Listed file E1491 (Guide Number NLDX2)



Product compliance: No Data

© 2016 Eaton. All rights reserved.