



Powering Business Worldwide

pe.eaton.com

Assembled Limit Switch

E49M11VP1

UPC:782113680965

Dimensions:

- **Height:** 1.58 IN
- **Length:** 8.22 IN
- **Width:** 1.63 IN

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 250 Vac, 1.5A at 24 Vdc
- **Mounting:** Standard DIN
- **Actuator:** Wobble
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die cast aluminum
- **Environmental Rating:** IP67
- **Maximum Ac Current:** 10A continuous
- **Maximum Dc Current:** 1.5A
- **Operating Speed:** 1 mm-2m/s
- **Operating Temperature:** 14° to 176°F
- **Series:** E49

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E49M11VP1](#)

Certifications: No Data

Product compliance: No Data

