



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## K-Factor Non Linear Transformer, Ventilated

**N29M28F15A**

**UPC:**786680014574

### Dimensions:

- **Height:** 30 IN
- **Length:** 16.5 IN
- **Width:** 23 IN

**Weight:**231 LB

**Notes:**Model A

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Special Features:** Electrostatically Shielded
- **Design:** K-13
- **Coil Material:** Aluminum windings
- **Frame:** 912B
- **Frequency Rating:** 60 Hz
- **Phase:** Three-phase
- **Primary Voltage:** 208V
- **Secondary Voltage:** 208Y/120V
- **Tap Size:** 2 at +2.5% FCAN, 4 at -2.5% FCBN
- **Temperature Rating:** 115°C
- **Volt Ampere Rating:** 15 KVA
- **Weathershield:** WS38

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - N29M28F15A](#)

### Certifications:

- UL Listed



**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.