



Powering Business Worldwide

pe.eaton.com

Inductive Proximity Sensor

E57-30JS10-H

UPC:782113027562

Dimensions:

- **Height:** 1.18 IN
- **Length:** 2.73 IN
- **Width:** 1.18 IN

Weight: .75 LB

Warranties:

- 1 year

Specifications:

- **Special Features:** Shielded
- **Type:** E57
- **Contact Rating:** 3.5A at 10-55 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** Complementary PNP open collector
- **Cord Length:** 79.2 FT
- **Enclosure Material:** 303 stainless steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12, 13, IP67
- **Input Voltage:** 10-55 Vdc
- **Led Indicators:** 360° visibility
- **Maximum Dc Current:** 3.5 A
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Protection:** Transient, power protection on false pulse
- **Temperature Rating:** -40° to 158°F

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57-30JS10-H](#)

Certifications: No Data

Product compliance: No Data



