



Powering Business Worldwide

pe.eaton.com

Photoelectric Sensor Connector Cable

CSAR4F4CY2205

UPC:782116056996

Dimensions:

- **Height:** 1 IN
- **Length:** 196.8 IN
- **Width:** .58 IN

Warranties:

- 1 year

Specifications:

- **Type:** Accessory
- **Connection:** Micro-style right angle female
- **Cable Type:** PVC
- **Cord Length:** 196.8 FT
- **Environmental Rating:** IP67
- **Input Voltage:** 320V
- **Number Of Pins:** 4 pin
- **Number Of Wires:** 4-wire
- **Operating Temperature:** -13° to 176°F (-25° to 80°C)
- **Power:** AC
- **Series:** Global Plus
- **Switch Type:** Sensor connectivity
- **Wire Size:** 22 AWG

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - CSAR4F4CY2205](#)

Certifications: No Data

Product compliance: No Data

