



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Perfect Prox Photoelectric Sensor

**E58-30DPS280-EL**

**UPC:782114557013**

### Dimensions:

- **Height:** 1.18 IN
- **Length:** 4.36 IN
- **Width:** 1.18 IN

### Warranties:

- 3 year

### Specifications:

- **Type:** Perfect Prox Photoelectric Sensor
- **Contact Rating:** 300 mA at 90-132 Vac/18-50 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** 2-wire AC/DC
- **Cord Length:** 79.2 FT
- **Enclosure Material:** 303 stainless steel
- **Environmental Rating:** NEMA 1, 2, 3, 3R, 3S, 4, 4X, 6, 6P, 12, 12K, 13, IP69K
- **Input Voltage:** 90-132 Vac 50/60 Hz, 18-50 Vdc
- **Led Indicators:** Output ON, flashes when latched
- **Maximum Ac Current:** 300 mA
- **Operating Temperature:** -10° to 131°F
- **Protection:** Auto reset S/C
- **Sensor Type:** Back Ground Suppression
- **Series:** E58

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Test the Best Photoelectric Sensors: E58 Series Harsh Duty](#)
- [Eaton Specification Sheet - E58-30DPS280-EL](#)



**Certifications:**

- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.