



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)



## Quicklag Industrial Thermal-Magnetic Circuit Breaker

**QHCX1040**

**UPC:**786679151532

### Dimensions:

- **Height:** .9 IN
- **Length:** 3.8 IN
- **Width:** 3 IN

**Weight:**.3 LB

### Warranties:

- 1 year

### Specifications:

- **Type:** Quicklag
- **Amperage Rating:** 40A
- **Interrupt Rating:** 42 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240V
- **Trip Type:** Non-Interchangeable
- **Circuit Breaker Type:** QHCX
- **Connection:** Cable-in/Cable-out

### Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - QHCX1040](#)

### Certifications:

- UL Listed
- CSA Certified

**Product compliance:** No Data