



Powering Business Worldwide

pe.eaton.com

Harsh Environment Safety Switch with Receptacle

DH362FDK2WRW

UPC:782114792094

Dimensions:

- **Height:** 10 IN
- **Length:** 30 IN
- **Width:** 13.75 IN

Weight:30 LB

Notes:Suitable for service entrance use with a neutral or ground lug kit installed. Can be field modified to meet NEMA 3R rainproof requirements when a factory provided drain hole is opened.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** Receptacle switch, Crouse-Hinds® ARKTITE, upper viewing window
- **Type:** Receptacle Switch, Crouse-Hinds ARKTITE® Receptacle
- **Amperage Rating:** 60A
- **Enclosure:** NEMA 12
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible without neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Three-wire
- **Product Category:** Heavy Duty, Fusible without neutral
- **Voltage Rating:** 600V
- **Max Hp Rating:** 20 at 480 Vac TD 1 Ph, 25 at



600 Vac TD 1 Ph, 30 at 480 Vac TD 3 Ph, 50 at
600 Vac TD 3 Ph

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DH362FDK2WRW](#)

Certifications:

- UL Listed

Product compliance: No Data