



Powering Business Worldwide

pe.eaton.com

UNIPAK, Low Voltage Fixed Capacitor Banks

2043PMURF

UPC:782116058693

Dimensions:

- **Height:** 22.3 IN
- **Length:** 5.954 IN
- **Width:** 8.5 IN

Weight:30.63 LB

Notes:Multiply the 240V kVAR rating by 0.75 to calculate the kVAR value at 208V.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** UNIPAK
- **Amperage Rating:** 24A
- **Enclosure:** NEMA 1, 3R
- **Enclosure Material:** 14 ga. steel finished w/durable powder coat finish
- **Frame Size:** A2
- **Fuse Type:** Three slottedblade type fuses with 200,000 ampere interrupting capacity, Fuses mounted on stand-off bushings or fuse blocks, solderless connectors for easy hookup of incoming line conductors.
- **Indicator:** Red, neon blown-fuse indicating lights are protected by transparent weatherproof guard
- **Phase:** Three-phase
- **Product Category:** Low Voltage Fixed Capacitor Banks



- **Protection:** Three fuses, three lights
- **Rating:** 20 kVAR
- **Voltage Rating:** 480V

Supporting documents:

- [Eatons Volume 3-Power Distribution and Control Assemblies](#)
- [Eaton Specification Sheet - 2043PMURF](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance: No Data