



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Type Visi-Flex Disconnect Switch

2607D89G12

UPC:786679990223

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

**Notes:** Shipped as basic switch, operating handle, shaft and fuse kit. Special 60Aere switch has same dimension as 30Aere Visi-Flex switch.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Disconnect switch
- **Amperage Rating:** 60A
- **Fuse Clip Rating:** 60A at 600 Vac
- **Fuse Configuration:** Fusible
- **Max Hp Rating:** 15 hp at 480 Vac, 15 hp at 600 Vac, 10 hp at 250 Vdc
- **Switch Type:** Visi-Flex DE-ION
- **Trip Type:** Model A trip
- **Wire Size:** #14-#4 Cu

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - 2607D89G12](#)

### Certifications:

- UL Listed

**Product compliance:** No Data



