



Powering Business Worldwide

pe.eaton.com

CN35 or A202 Enclosed Lighting Contactor

ECL03B1B3A

UPC:782114072509

Dimensions:

- **Height:** 9.51 IN
- **Length:** 5.62 IN
- **Width:** 5.71 IN

Weight:5.2 LB

Notes: Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 20A
- **Coil Voltage:** 220V/50 Hz, 240V/60 Hz
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Frame Size:** 45 mm
- **Number Of Poles:** Three-pole
- **Type:** Non-combination electrically held

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Lighting contactors](#)
- [Eaton Specification Sheet - ECL03B1B3A](#)

Certifications:

- cUL Listed
- UL Listed

Product compliance: No Data



