



Powering Business Worldwide

pe.eaton.com

Continuous Duty AC Solenoid

10370H370

UPC:782113236247

Dimensions:

- **Height:** 6.13 IN
- **Length:** 3.75 IN
- **Width:** 3.88 IN

Notes: Mounting of solenoids “with conduit box”—Size A are for wall mounting—Size B, C and D are for floor mounting.

Warranties:

- 1 year

Specifications:

- **Magnetic Force Against Gravity:** 11.15 lbs at 100% voltage, 8.75 lbs at 85% voltage
- **Magnetic Force Horizontal:** 12.4 lbs at 100% voltage, 10 lbs at 85% voltage
- **Magnetic Force With Gravity:** 13.65 lbs at 100% voltage, 11.25 lbs at 85% voltage
- **Frequency Rating:** 60 Hz
- **Full Load Current Range:** Inrush 4.4A/Sealed ..40A
- **Mounting:** Floor mount
- **Operation:** Pull type
- **Size:** D
- **Special Features:** With conduit box
- **Voltage Rating:** 440A

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - 10370H370](#)

Certifications: No Data

Product compliance: No Data



