



Powering Business Worldwide

pe.eaton.com

SM Series Rectangular Body Photoelectric Sensor

E65-SMTS15-HAD

UPC:782114786543

Dimensions:

- **Height:** 1.29 IN
- **Length:** 2.17 IN
- **Width:** 1.47 IN

Weight:.0688 LB

Notes:For complete system; order 1 source and 1 detector

Warranties:

- 3 year

Specifications:

- **Type:** Photoelectric Sensor; SM Series
- **Connection:** 4 Pin M12 Connector
- **Cable Type:** PVC
- **Enclosure Material:** Lens: polycarbonate cable jacket: PVC body: Cycloy
- **Environmental Rating:** NEMA 1,3,4,4X,6,6P,12,13, IP68, IP69K
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Green power on
- **Operating Mode:** Thru-beam
- **Operating Temperature:** -13° to 131°F (-25° to 55°C)
- **Sensor Type:** Through Beam
- **Switch Type:** Photoelectric

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Test the Best Photoelectric Sensors: SM Series](#)
- [Eaton Specification Sheet - E65-SMTS15-HAD](#)

Certifications:

- cUL Listed



- UL Listed

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.