



Powering Business Worldwide

pe.eaton.com

House Panel

HP40SHA

UPC:782116060108

Dimensions:

- **Height:** 40.2 IN
- **Length:** 30 IN
- **Width:** 6.5 IN

Weight:120 LB

Notes:For 10 kAIC, use BR or BW breakers as secondary main. Confirm security type for individual EUSERC utility requirements. Load conductors can exit the top, bottom, side or back. Secondary breaker not included.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 400A
- **Bus Material:** Aluminum
- **Bypass:** Manual bypass
- **Enclosure:** NEMA 3R
- **Feed Type:** Underground
- **Interrupt Rating:** 22 kAIC
- **Line:** Lug landings for compression, lugs not included
- **Main Circuit Breaker:** CSR2200
- **Mounting:** Surface mounting
- **Number Of Sockets:** 1
- **Secondary Circuit Breaker:** BRH/BWH
- **Security:** Ring
- **Used With:** Type BR breakers
- **Voltage Rating:** 120/240V



Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - HP40SHA](#)

Certifications:

- UL Listed

Product compliance:

- EUSERC Approved

© 2016 Eaton. All rights reserved.