



Powering Business Worldwide

pe.eaton.com

Harsh Environment Safety Switch with Viewing Window

DH364NDKW

UPC:782114136645

Dimensions:

- **Height:** 35.38 IN
- **Length:** 11.63 IN
- **Width:** 15.5 IN

Weight:61 LB

Notes:For 2-pole applications; use outside poles of 3-pole switch. Can be field modified to meet NEMA 3R rainproof requirements when a factory provided drain hole is opened.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** Upper viewing window
- **Type:** Single-Throw
- **Amperage Rating:** 200A
- **Enclosure:** NEMA 12
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible with neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Four-wire
- **Product Category:** Heavy Duty, Fusible with neutral
- **Voltage Rating:** 600V
- **Max Hp Rating:** 50 at 480 Vac TD 1 Ph, 50 at 600 Vac TD 1 Ph, 125 at 480 Vac TD 3 Ph, 150 at 600 Vac TD 3 Ph



Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DH364NDKW](#)

Certifications:

- UL Listed

Product compliance: No Data