



Powering Business Worldwide

pe.eaton.com

Type Visi-Flex Disconnect Switch

2607D89G02

UPC:786679990124

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes: Shipped as basic switch, operating handle, shaft and fuse kit

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Disconnect switch
- **Amperage Rating:** 30A
- **Fuse Clip Rating:** 30A at 250 Vac
- **Fuse Configuration:** Fusible
- **Max Hp Rating:** 1-1/2 hp at 120 Vac, 3 hp at 240 Vac, 5 hp at 250 Vdc
- **Switch Type:** Visi-Flex DE-ION
- **Trip Type:** Model A trip
- **Wire Size:** #14-#4 Cu

Supporting documents:

- [Eaton's Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - 2607D89G02](#)

Certifications:

- UL Listed

Product compliance: No Data



