



Powering Business Worldwide

pe.eaton.com

CLT type current limiting fuse

15CLT-30

UPC:786670501701

Dimensions:

- **Height:** X
- **Length:** 9.76 IN
- **Width:** X

Notes:Consult factory for mountings.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** CLT
- **Barrels:** Single barrel
- **Diameter:** 2.25 IN
- **Interrupt Rating:** 25 kA
- **Amperage Rating:** 30A
- **Maximum Voltage:** 15.5 kV
- **Nominal Voltage:** 14.4 kV

Supporting documents:

- [Eatons Volume 14-Fuses](#)
- [Medium voltage power fuses](#)
- [Eaton Specification Sheet - 15CLT-30](#)

Certifications:

- IEEE Std. C37.41

Product compliance: No Data

