



Powering Business Worldwide

pe.eaton.com

30.5 mm, Heavy-Duty Pushbutton Operator

10250T397LGD24

UPC:782114753811

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes: Unit does not include lamp. Order LED separately to match lens.

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator Color:** Green
- **Actuator Material:** Plastic
- **Bezel:** Chrome
- **Illumination:** Illuminated
- **Lamp Voltage:** 24 Vac/dc
- **Led Lamp Number:** Bayonet base
- **Light Unit Type:** LED, full voltage
- **Mounting:** Flush
- **Operating Mode:** Momentary
- **Size:** 40 mm
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T

Supporting documents:

- [Eaton's Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T397LGD24](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance:



- CE Marked

© 2016 Eaton. All rights reserved.