



Powering Business Worldwide

pe.eaton.com

Harsh Environment Safety Switch with Viewing Window

DH363NDKW2

UPC:786679163986

Dimensions:

- **Height:** 8 IN
- **Length:** 25.5 IN
- **Width:** 13.25 IN

Weight:28 LB

Notes:For 2-pole applications; use outside poles of 3-pole switch. Can be field modified to meet NEMA 3R rainproof requirements when a factory provided drain hole is opened.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** Upper viewing window
- **Type:** Single-Throw
- **Amperage Rating:** 100A
- **Enclosure:** NEMA 12
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible with neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Four-wire
- **Product Category:** Heavy Duty, Fusible with neutral
- **Voltage Rating:** 600V
- **Max Hp Rating:** 30 at 480 Vac TD 1 Ph, 40 at 600 Vac TD 1 Ph, 60 at 480 Vac TD 3 Ph, 75 at 600 Vac TD 3 Ph



Supporting documents:

- [Eaton Specification Sheet - DH363NDKW2](#)

Certifications:

- UL 98

Product compliance: No Data