



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E56 Series Pancake Style Inductive Proximity Sensor

**E56CDL40A2B1**

**UPC:**782113915784

### Dimensions:

- **Height:** 3.13 IN
- **Length:** 3.87 IN
- **Width:** 1.54 IN

**Weight:**.8188 LB

### Warranties:

- 1 year

### Specifications:

- **Accuracy:** < 2%
- **Connection:** 3 Pin Mini Connector
- **Contact Rating:** 400 mA at 250 Vac
- **Contact Configuration:** 2 - Wire AC, Normally Open or Normally Closed
- **Enclosure Material:** PPS housing
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12 and 13 (IP67)
- **Input Voltage:** 20-250 Vac
- **Led Indicators:** Output Status
- **Maximum Ac Current:** 400 mA
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Short circuit protection with auto reset
- **Sensor Type:** Inductive Proximity

### Supporting documents:

- [E52Q Cube and E56 Pancake inductive sensors](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E56CDL40A2B1](#)



**Certifications:** No Data

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.