



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E51 Series Factory Sealed Pre-Wired Switch Body

**E51SCL6P**

**UPC:**782113310251

### Dimensions:

- **Height:** 3.14 IN
- **Length:** 1.54 IN
- **Width:** 1.73 IN

**Weight:**.3938 LB

### Warranties:

- 1 year

### Specifications:

- **Connection:** 8 Ft. ( 2.5m ) Cable
- **Contact Rating:** 1.0A Solid State Output
- **Cable Type:** SOOW-A
- **Contact Configuration:** L1 Switched
- **Cord Length:** 96 FT
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 3,3S,4,4X,6,6P,12,13, IP67
- **Input Voltage:** 120Vac
- **Led Indicators:** Lights when output is ON. One LED for each output
- **Maximum Ac Current:** 1.0A
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** None

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E51SCL6P](#)

### Certifications:

- UL Listed
- CSA Certified



**Product compliance:**

- CE Marked

---

© 2016 Eaton. All rights reserved.