



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 30.5 mm, Heavy-Duty Pushbutton Operator

10250T411LGD06

UPC:782114709702

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

### Warranties:

- 1 year

### Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator Color:** Green
- **Actuator Material:** Plastic
- **Bezel:** Chrome
- **Illumination:** Illuminated
- **Lamp Voltage:** 6 Vac/dc
- **Led Lamp Number:** Bayonet base
- **Light Unit Type:** LED, transformer
- **Light Unit Voltage:** 120 Vac
- **Mounting:** Flush
- **Operating Mode:** Momentary
- **Size:** 40 mm
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T411LGD06](#)

### Certifications:

- CSA Certified
- UL Listed

### Product compliance:

- CE Marked



